

Dear optician, optometrist and colleague,



We are writing to you from the contact lens laboratory Tiedra Farmacéutica S.L. to inform you about our ALEXA AR® contact lens, which your patient is interested in trying.

ALEXA AR® is a contact lens designed specifically for overnight use. It gets to work while you are sleeping to ensure normal vision when you wake so you don't have to wear glasses or contact lenses during the day.

ALEXA AR® is made according to the biometric parameters of each eye.

ALEXA AR® are custom-made contact lenses. ALEXA AR® are made for each wearer according to the anatomical characteristics of their eyes. This means that each person wears a contact lens that perfectly adapts to the anatomy of their eyes and their vision needs.

This guarantees safe and effective compensation for their myopia, hypermetropia and/or astigmatism.



ALEXA AR® is designed with four state-of-the-art curves that allow for corrections of up to -5.00 D, providing a simple, parametrised and optimised fit.

Material	Colour	Hardness	Wetting angle	Refractive index	Dk	Diameter (mm)
HDS 100 (Paflucocon D)	Blue/ Yellow/ Red	79	42	1.44	100	9.80 to 12.40



ALEXA® AR Plus is designed with five state-of-the-art curves that allow for corrections of up to -5.00 to -10.00 D, providing a parametrised and optimised fit.

Material	Colour	Hardness	Wetting angle	Refractive index	Dk	Diameter (mm)
HDS 100 (Paflucocon D)	Blue/ Yellow/ Red	79	42	1.44	100	9.80 to 12.40

If you require additional information or would like to order your first contact lenses, contact us by email at pedidos@tiedra.net or by phone on +34 916434140.

Kind regards,
Tiedra Farmacéutica S.L.

